

# PRODUCT INFORMATION PACKET

Model No: 444PART8803  
Catalog No: 444PART8803  
PARTIAL MOTOR

Regal and are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E



**Nameplate Specifications**

Output HP	N Hp	Frequency	0 Hz
Voltage	0 V	Current	N/A A
Speed	3600 rpm	Phase	3
Duty	NONE	Insulation Class	NONE
Design Code	NO DESIGN CODE	KVA Code	N
Frame	444TSC	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Ambient Temperature	40 °C
Drive End Bearing Size	313	Opp Drive End Bearing Size	313
UL	No	CSA	Y
CE	Y	IP Code	43
Number of Speeds	1		

**Technical Specifications**

Electrical Type	Squirrel Cage Induction Run	Starting Method	NONE
Poles	2	Rotation	NONE
Mounting	Rigid Base	Motor Orientation	Horizontal
Frame Material	Cast Iron	Assembly/Box Mounting	F1/F2 CAPABLE
Connection Drawing	NONE	Outline Drawing	NONE

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/18/2022