

PRODUCT INFORMATION PACKET

Model No: 445PART8006
Catalog No: 445PART8006
PARTIAL MOTOR

Regal and are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E



Nameplate Specifications

Output HP	N Hp	Frequency	0 Hz
Voltage	0 V	Current	N/A A
Speed	3600 rpm	Duty	NONE
Insulation Class	NONE	Design Code	NO DESIGN CODE
KVA Code	N	Frame	445TSC
Enclosure	Totally Enclosed Fan Cooled	Thermal Protection	No Protection
Ambient Temperature	40 °C	Drive End Bearing Size	NONE
Opp Drive End Bearing Size	NONE	UL	No
CSA	Y	CE	N
IP Code	43	Number of Speeds	1

Technical Specifications

Electrical Type	NONE	Starting Method	NONE
Rotation	NONE	Mounting	Rigid Base
Motor Orientation	Horizontal	Frame Material	Cast Iron
Assembly/Box Mounting	F1/F2 CAPABLE		
Connection Drawing	NONE	Outline Drawing	NONE

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/18/2022