

PRODUCT INFORMATION PACKET

Model No: 447PART7011
Catalog No: 447PART7011
400,3600,DP,447TCZ,3/60/460 - PARTIAL MOTOR

Regal and are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E



Nameplate Specifications

Output HP	400 Hp	Output KW	300.0 kW
Frequency	60 Hz	Voltage	460 V
Current	435.0 A	Speed	3568 rpm
Phase	3	Efficiency	95.4 %
Power Factor	88.5	Duty	NONE
Insulation Class	NONE	Design Code	NO DESIGN CODE
KVA Code	F	Frame	447TCZ
Enclosure	PARTIAL	Thermal Protection	No Protection
Ambient Temperature	40 °C	Drive End Bearing Size	NONE
Opp Drive End Bearing Size	NONE	UL	No
CSA	Y	CE	Y
IP Code	12	Number of Speeds	1

Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	NONE
Poles	2	Rotation	NONE
Resistance Main	.0105 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Frame Material	Cast Iron
Shaft Type	Single Special Extension	Assembly/Box Mounting	F1/F2 CAPABLE
Outline Drawing	NONE	Connection Drawing	NONE

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/18/2022