

PRODUCT INFORMATION PACKET

Model No: 6KHF9
Catalog No: 6KHF9
MODEL-IHP

Regal and are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E



Nameplate Specifications

Output HP	5.0-7.0 Hp	Output KW	3.7 kW
Frequency	60 Hz	Voltage	200-230 V
Current	32-28 A	Speed	3440 rpm
Service Factor	1	Phase	1
Duty	Continuous	Insulation Class	F
Frame	S184TZ	Enclosure	Open Drip Proof
Thermal Protection	PILOT DUTY	Ambient Temperature	50 °C
UL	Recognized	CSA	Y

Technical Specifications

Poles	2	Rotation	CW-CCW
Mounting	Rigid Base	Drive End Bearing	Ball
Shaft Extension	1 1/8 KEY in		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/18/2022