



### Nameplate Specifications

|                        |                             |                            |                             |
|------------------------|-----------------------------|----------------------------|-----------------------------|
| Output HP              | 7.5 Hp                      | Output KW                  | 5.5 kW                      |
| Frequency              | 50 Hz                       | Voltage                    | D400/Y690 V                 |
| Current                | 10.50 A                     | Speed                      | 1475 rpm                    |
| Service Factor         | 1                           | Phase                      | 3                           |
| Efficiency             | 89.6 %                      | Power Factor               | 0.84                        |
| Duty                   | S1                          | Insulation Class           | F                           |
| Frame                  | 132S                        | Enclosure                  | Totally Enclosed Fan Cooled |
| Thermal Protection     | No Protection               | Ambient Temperature        | 40 °C                       |
| Drive End Bearing Size | 6308-2Z/C3WT (-40°C/+160°C) | Opp Drive End Bearing Size | 6308-2Z/C3WT (-40°C/+160°C) |
| UL                     | No                          | CSA                        | Optional                    |
| CE                     | Yes                         | IP Code                    | IP55                        |
| Number of Speeds       | 1                           | Efficiency Class           | IE3                         |

### Technical Specifications

|                 |               |                   |                     |
|-----------------|---------------|-------------------|---------------------|
| Electrical Type | Squirrel Cage | Starting Method   | Direct On Line      |
| Poles           | 4             | Rotation          | Clockwise Shaft End |
| Mounting        | B3            | Motor Orientation | Any                 |
| Frame Material  | Cast iron     | Shaft Type        | Keyed               |
| Shaft Diameter  | 38 mm         | Shaft Extension   | 80 mm               |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:12/02/2022