



Nameplate Specifications

Output HP	60.00 Hp	Output KW	45.0 kW
Frequency	50 Hz	Voltage	D230/Y400 V
Current	140.94 A	Speed	1485 rpm
Service Factor	1	Phase	3
Efficiency	95.4 %	Power Factor	0.84
Duty	S1	Insulation Class	F
Frame	225M	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Ambient Temperature	40 °C
Drive End Bearing Size	6313/C3	Opp Drive End Bearing Size	6313/C3
UL	No	CSA	Optional
CE	Yes	IP Code	IP55
Number of Speeds	1	Efficiency Class	IE4

Technical Specifications

Electrical Type	Squirrel Cage	Starting Method	Direct On Line
Poles	4	Rotation	Clockwise Shaft End
Mounting	B3	Motor Orientation	Any
Frame Material	Cast iron	Shaft Type	Keyed

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:01/19/2023