



Nameplate Specifications

Output HP	120.00 Hp	Output KW	90.0 kW
Frequency	50 Hz	Voltage	D230/Y400 V
Current	273.00 A	Speed	1485 rpm
Service Factor	1	Phase	3
Efficiency	95.2 %	Power Factor	0.86
Duty	S1	Insulation Class	F
Frame	280M	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Ambient Temperature	40 °C
Drive End Bearing Size	6317/C3	Opp Drive End Bearing Size	6317/C3
UL	No	CSA	Optional
CE	Yes	IP Code	IP55
Number of Speeds	1	Efficiency Class	IE3

Technical Specifications

Electrical Type	Squirrel Cage	Starting Method	Direct On Line
Poles	4	Rotation	Clockwise Shaft End
Mounting	B35	Motor Orientation	Any
Frame Material	Cast iron	Shaft Type	Keyed
Shaft Diameter	75 mm	Shaft Extension	140 mm
Outline Drawing	6RN280M04E32_2021		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:01/19/2023