



Nameplate Specifications

Output HP	120 Hp	Output KW	90.0 kW
Frequency	50 Hz	Voltage	D400/Y690 V
Current	157.50 A	Speed	1485 rpm
Service Factor	1	Phase	3
Efficiency	95.2 %	Power Factor	0.86
Duty	S1	Insulation Class	F
Frame	280M	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Ambient Temperature	40 °C
Drive End Bearing Size	6317/C3	Opp Drive End Bearing Size	6317/C3
UL	No	CSA	Optional
CE	Yes	IP Code	IP55
Number of Speeds	1	Efficiency Class	IE3

Technical Specifications

Electrical Type	Squirrel Cage	Starting Method	Direct On Line
Poles	4	Rotation	Clockwise Shaft End
Mounting	B5	Motor Orientation	Any
Frame Material	Cast iron	Shaft Type	Keyed
Shaft Diameter	75 mm	Shaft Extension	140 mm
Outline Drawing	6RN280M04E32U463021		

This is an uncontrolled document once printed or downloaded and is
subject to change without notice. Date Created:01/19/2023