

Nameplate Specifications

Output HP	270 Hp	Output KW	200.0 kW
Frequency	50 Hz	Voltage	D400 V
Current	330.00 A	Speed	2986 rpm
Service Factor	1	Phase	3
Efficiency	95.8 %	Power Factor	0.90
Duty	S1	Insulation Class	F
Frame	315L	Enclosure	Totally Enclosed Fan Cooled
Ambient Temperature	40 °C	Drive End Bearing Size	6316/C3
Opp Drive End Bearing Size	6316/C3	UL	No
CSA	Optional	CE	Yes
IP Code	IP55	Number of Speeds	1
Efficiency Class	IE3		

Technical Specifications

Electrical Type	Squirrel Cage	Starting Method	Direct On Line
Poles	2	Rotation	Clockwise Shaft End
Mounting	V1	Motor Orientation	Any
Frame Material	Cast iron	Shaft Type	Keyed

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:12/27/2021