



## Nameplate Specifications

|                        |               |                            |                             |
|------------------------|---------------|----------------------------|-----------------------------|
| Output HP              | 175.00 Hp     | Output KW                  | 132.0 kW                    |
| Frequency              | 50 Hz         | Voltage                    | D400/Y690 V                 |
| Current                | 237.50 A      | Speed                      | 991 rpm                     |
| Service Factor         | 1             | Phase                      | 3                           |
| Efficiency             | 95.4 %        | Power Factor               | 0.84                        |
| Duty                   | S1            | Insulation Class           | F                           |
| Frame                  | 315L          | Enclosure                  | Totally Enclosed Fan Cooled |
| Thermal Protection     | No Protection | Ambient Temperature        | 40 °C                       |
| Drive End Bearing Size | 6319/C3       | Opp Drive End Bearing Size | 6319/C3                     |
| UL                     | No            | CSA                        | Optional                    |
| CE                     | Yes           | IP Code                    | IP55                        |
| Number of Speeds       | 1             | Efficiency Class           | IE3                         |

## Technical Specifications

|                 |                   |                   |                     |
|-----------------|-------------------|-------------------|---------------------|
| Electrical Type | Squirrel Cage     | Starting Method   | Direct On Line      |
| Poles           | 6                 | Rotation          | Clockwise Shaft End |
| Mounting        | B3                | Motor Orientation | Any                 |
| Frame Material  | Cast iron         | Shaft Type        | Keyed               |
| Shaft Diameter  | 80 mm             | Shaft Extension   | 170 mm              |
| Outline Drawing | 6RN315L06E35_1041 |                   |                     |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:01/19/2023