



Nameplate Specifications

| | | | |
|--------------------|------------|---------------------|-----------------------------|
| Output HP | 75 Hp | Output KW | 56.0 kW |
| Frequency | 60 Hz | Voltage | 208-230/460 V |
| Current | 89 A | Speed | 1188 rpm |
| Service Factor | 1.15 | Phase | 3 |
| Duty | Continuous | Insulation Class | F |
| Frame | 405TC | Enclosure | Totally Enclosed Fan Cooled |
| Thermal Protection | None | Ambient Temperature | 40 °C |
| UL | Recognized | CSA | Y |
| CE | Y | Number of Speeds | 1 |

Technical Specifications

| | | | |
|-----------------------|------------|--------------------|-----------------|
| Electrical Type | POLYPHASE | Starting Method | Across The Line |
| Poles | 6 | Rotation | Reversible |
| Mounting | Rigid Base | Drive End Bearing | Ball |
| Opp Drive End Bearing | Ball | Frame Material | Cast Iron |
| Shaft Type | Keyed | Overall Length | 42.76 in |
| Frame Length | 21.65 in | Shaft Diameter | 2.875 in |
| Shaft Extension | 7.25 in | | |
| Outline Drawing | SS620306 | Connection Drawing | A-EE7308AA |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/07/2021