

PRODUCT INFORMATION PACKET



Model No: E3035
Catalog No: E3035
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E





Nameplate Specifications

Phase	3	Output HP	40.0 Hp
Output KW	29.8 kW	Voltage	230/460 V
Speed	3550 r/min	Service Factor	1.15
Frame	324TSC	Thermal Protection	No Protection
Efficiency	91.7 %	Ambient Temperature	40 °C
Frequency	60 Hz	Current	88/44 A
Duty	Continuous	Insulation Class	F

Technical Specifications

Rotation	Reversible	Drive End Bearing	313
Opp Drive End Bearing	311		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025