

Nameplate Specifications

Output HP	0.34 Hp	Output KW	0.25 kW
Frequency	50 Hz	Voltage	230/400 V
Current	0.73 A	Speed	1405 rpm
Service Factor	1	Phase	3
Efficiency	73.5 %	Power Factor	0.69
Duty	S1	Insulation Class	F
Frame	71A	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Ambient Temperature	40 °C
Drive End Bearing Size	6203	Opp Drive End Bearing Size	6203
UL	No	CSA	No
CE	Yes	IP Code	IP55
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage	Starting Method	Direct On Line
Poles	4	Rotation	Bi-Directional
Mounting	B3	Motor Orientation	Horizontal
Drive End Bearing	Zz	Opp Drive End Bearing	Zz
Frame Material	Cast Iron	Shaft Type	Keyed
Overall Length	311.00 mm	Frame Length	112.00 mm
Shaft Diameter	14.000 mm	Shaft Extension	30 mm
Assembly/Box Mounting	Top		
Outline Drawing	B3A048070001A01	Connection Drawing	SC-01-T-1v-1a