

Nameplate Specifications

Output HP	0.74 Hp	Output KW	0.55 kW
Frequency	50 Hz	Voltage	230/400 V
Current	1.3 A	Speed	1434 rpm
Service Factor	1	Phase	3
Efficiency	83.6 %	Power Factor	0.75
Duty	S1	Insulation Class	F
Frame	80MA	Enclosure	Totally Enclosed Fan Cooled
Ambient Temperature	40 °C	Drive End Bearing Size	6204
Opp Drive End Bearing Size	6204	UL	No
CSA	No	CE	Yes
IP Code	IP55	Number of Speeds	1

Technical Specifications

Electrical Type	Squirrel Cage	Starting Method	Direct On Line
Poles	4	Rotation	Bi-Directional
Mounting	B5	Motor Orientation	Horizontal
Drive End Bearing	Zz	Opp Drive End Bearing	Zz
Frame Material	Cast Iron	Shaft Type	Keyed
Overall Length	401.00 mm	Frame Length	195.00 mm
Shaft Diameter	19.000 mm	Shaft Extension	40 mm
Assembly/Box Mounting	Top		
Outline Drawing	B5A04E8080001B01	Connection Drawing	SC-01-T-1v-1a