

## Nameplate Specifications

Output HP	0.24 Hp	Output KW	0.18 kW
Frequency	50 Hz	Voltage	230/400 V
Current	0.59 A	Speed	1334 rpm
Service Factor	1	Phase	3
Efficiency	69.9 %	Power Factor	0.63
Duty	S1	Insulation Class	F
Frame	63B	Enclosure	Totally Enclosed Fan Cooled
Ambient Temperature	40 °C	Drive End Bearing Size	6202
Opp Drive End Bearing Size	6202	UL	No
CSA	No	CE	Yes
IP Code	IP55	Number of Speeds	1

## Technical Specifications

Electrical Type	Squirrel Cage	Starting Method	Direct On Line
Poles	4	Rotation	Bi-Directional
Mounting	B3	Motor Orientation	Horizontal
Drive End Bearing	Zz	Opp Drive End Bearing	Zz
Frame Material	Cast Iron	Shaft Type	Keyed
Overall Length	275.50 mm	Frame Length	105.00 mm
Shaft Diameter	11.000 mm	Shaft Extension	23 mm
Assembly/Box Mounting	Top		
Connection Drawing	SC-01-T-1v-1a	Outline Drawing	B3A048060001A01