

## Nameplate Specifications

Phase	3	Output HP	0.7375621 Hp
Output KW	0.55 kW	Voltage	230/400 V
Speed	955 rpm	Service Factor	1
Frame	80B	Enclosure	Totally Enclosed Fan Cooled
Efficiency	77.2 %	Ambient Temperature	40 °C
Frequency	50 Hz	Power Factor	0.74
Duty	S1	Insulation Class	F
Drive End Bearing Size	6204	Opp Drive End Bearing Size	6204
UL	No	CSA	No
CE	Yes	IP Code	IP55
Number of Speeds	1		

## Technical Specifications

Electrical Type	Squirrel Cage	Starting Method	Direct On Line
Poles	6	Rotation	Bi-Directional
Mounting	B35	Motor Orientation	Horizontal
Drive End Bearing	Zz	Opp Drive End Bearing	Zz
Frame Material	Cast Iron	Shaft Type	Keyed
Overall Length	373.00 mm	Frame Length	130.00 mm
Shaft Diameter	19.000 mm	Shaft Extension	40 mm
Assembly/Box Mounting	Top		
Connection Drawing	SC-01-T-1v-1a	Outline Drawing	B3A04E8080001D01