

Nameplate Specifications

| | | | |
|------------------------|---------------|----------------------------|-----------------------------|
| Output HP | 2 Hp | Output KW | 1.5 kW |
| Frequency | 50 Hz | Voltage | 230/400 V |
| Current | 3.0 A | Speed | 2870 rpm |
| Service Factor | 1 | Phase | 3 |
| Efficiency | 84.8 % | Power Factor | 0.84 |
| Duty | S1 | Insulation Class | F |
| Frame | 90S | Enclosure | Totally Enclosed Fan Cooled |
| Thermal Protection | No Protection | Ambient Temperature | 40 °C |
| Drive End Bearing Size | 6205 | Opp Drive End Bearing Size | 6205 |
| UL | No | CSA | No |
| CE | Yes | IP Code | IP55 |
| Number of Speeds | 1 | Efficiency Class | IE3 |

Technical Specifications

| | | | |
|-----------------------|---------------|-----------------------|------------------|
| Electrical Type | Squirrel Cage | Starting Method | Direct On Line |
| Poles | 2 | Rotation | Bi-Directional |
| Mounting | B3 | Motor Orientation | Horizontal |
| Drive End Bearing | 2z-C3 | Opp Drive End Bearing | 2z-C3 |
| Frame Material | Cast Iron | Shaft Type | Keyed |
| Overall Length | 307.00 mm | Frame Length | 128.00 mm |
| Shaft Diameter | 24.000 mm | Shaft Extension | 50 mm |
| Assembly/Box Mounting | Top | | |
| Connection Drawing | SC-01-T-1v-1a | Outline Drawing | B3A04T8095001A01 |