

Nameplate Specifications

| | | | |
|------------------------|---------------|----------------------------|-----------------------------|
| Output HP | 425 Hp | Output KW | 315.0 kW |
| Frequency | 50 Hz | Voltage | 400/690 V |
| Current | 534.1 A | Speed | 1491 rpm |
| Service Factor | 1 | Phase | 3 |
| Efficiency | 96 % | Power Factor | 0.89 |
| Duty | S1 | Insulation Class | F |
| Frame | 355LB | Enclosure | Totally Enclosed Fan Cooled |
| Thermal Protection | No Protection | Ambient Temperature | 40 °C |
| Drive End Bearing Size | 6322 | Opp Drive End Bearing Size | 6322 |
| UL | No | CSA | No |
| CE | Yes | IP Code | IP55 |
| Number of Speeds | 1 | | |

Technical Specifications

| | | | |
|-----------------------|---------------|-----------------------|------------------|
| Electrical Type | Squirrel Cage | Starting Method | Direct On Line |
| Poles | 4 | Rotation | Bi-Directional |
| Mounting | B5 | Motor Orientation | Horizontal |
| Drive End Bearing | C3 | Opp Drive End Bearing | C3 |
| Frame Material | Cast Iron | Shaft Type | Keyed |
| Overall Length | 1542.00 mm | Frame Length | 1010.00 mm |
| Shaft Diameter | 95.000 mm | Shaft Extension | 170 mm |
| Assembly/Box Mounting | Top | | |
| Connection Drawing | SC-01-T-1v-1a | Outline Drawing | B5A04T8350011B01 |