

Nameplate Specifications

Phase	3	Output HP	1.50 Hp
Output KW	1.1 kW	Voltage	230/400 V
Speed	719 rpm	Service Factor	1
Frame	100LB	Enclosure	Totally Enclosed Fan Cooled
Efficiency	77.7 %	Ambient Temperature	40 °C
Frequency	50 Hz	Current	2.9 A
Power Factor	0.71	Duty	S1
Insulation Class	F	UL	No
CSA	No	CE	Yes
IP Code	IP55	Number of Speeds	1

Technical Specifications

Electrical Type	Squirrel Cage	Starting Method	Direct On Line
Poles	8	Rotation	Bi-Directional
Mounting	B3	Motor Orientation	Horizontal
Frame Material	Cast Iron	Shaft Type	Keyed
Assembly/Box Mounting	Top		
Connection Drawing	SC-01-T-1v-1a		