

### Nameplate Specifications

Phase	<b>3</b>	Output HP	<b>10 Hp</b>
Output KW	<b>7.5 kW</b>	Voltage	<b>400/690 V</b>
Speed	<b>728 rpm</b>	Service Factor	<b>1</b>
Frame	<b>160L</b>	Enclosure	<b>Totally Enclosed Fan Cooled</b>
Efficiency	<b>87.8 %</b>	Ambient Temperature	<b>40 °C</b>
Frequency	<b>50 Hz</b>	Current	<b>16.7 A</b>
Power Factor	<b>0.74</b>	Duty	<b>S1</b>
Insulation Class	<b>F</b>	UL	<b>No</b>
CSA	<b>No</b>	CE	<b>Yes</b>
IP Code	<b>IP55</b>	Number of Speeds	<b>1</b>

### Technical Specifications

Electrical Type	<b>Squirrel Cage</b>	Starting Method	<b>Direct On Line</b>
Poles	<b>8</b>	Rotation	<b>Bi-Directional</b>
Mounting	<b>B3</b>	Motor Orientation	<b>Horizontal</b>
Frame Material	<b>Cast Iron</b>	Shaft Type	<b>Keyed</b>
Assembly/Box Mounting	<b>Top</b>		
Connection Drawing	<b>SC-01-T-1v-1a</b>		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/10/2023