

### Nameplate Specifications

Phase	3	Output HP	25 Hp
Output KW	18.5 kW	Voltage	400/690 V
Speed	738 rpm	Service Factor	1
Frame	225S	Enclosure	Totally Enclosed Fan Cooled
Efficiency	91.1 %	Ambient Temperature	40 °C
Frequency	50 Hz	Current	37.1 A
Power Factor	0.79	Duty	S1
Insulation Class	F	UL	No
CSA	No	CE	Yes
IP Code	IP55	Number of Speeds	1

### Technical Specifications

Electrical Type	Squirrel Cage	Starting Method	Direct On Line
Poles	8	Rotation	Bi-Directional
Mounting	B3	Motor Orientation	Horizontal
Frame Material	Cast Iron	Shaft Type	Keyed
Assembly/Box Mounting	Top		
Connection Drawing	SC-01-T-1v-1a		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/10/2023