

PRODUCT INFORMATION PACKET



Model No: E482M2A

Catalog No: E482M2A

15.0 HP Close-Coupled Pump Motor, 3 phase, 1800 RPM, 230/460 V, 254JM Frame, ODP
Close-Coupled Pump Motors



Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2021 Regal Rexnord Corporation, All Rights Reserved. MC017097E





Nameplate Specifications

Output HP	15.0 Hp	Output KW	11.2 kW
Frequency	60 Hz	Voltage	230/460 V
Current	37.8/18.9 A	Speed	1770 rpm
Service Factor	1.15	Phase	3
Duty	Continuous	Insulation Class	F
Frame	254JM	Enclosure	Drip Proof
Thermal Protection	None	Ambient Temperature	40 °C
UL	Recognized	CSA	Y
CE	Y	Number of Speeds	1

Technical Specifications

Electrical Type	Three Phase	Starting Method	Across The Line
Poles	4	Rotation	Counterclockwise
Mounting	Rigid Base	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Keyed	Overall Length	23.60 in
Frame Length	13.00 in	Shaft Diameter	1.750 in
Shaft Extension	5.25 in		
Connection Drawing	80022801.PCX	Outline Drawing	E482M2A-S01

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/12/2021

