



### Nameplate Specifications

|                    |             |                     |            |
|--------------------|-------------|---------------------|------------|
| Output HP          | 15.0 Hp     | Output KW           | 11.2 kW    |
| Frequency          | 60 Hz       | Voltage             | 230/460 V  |
| Current            | 37.8/18.9 A | Speed               | 1770 rpm   |
| Service Factor     | 1.15        | Phase               | 3          |
| Duty               | Continuous  | Insulation Class    | F          |
| Frame              | J254P       | Enclosure           | Drip Proof |
| Thermal Protection | None        | Ambient Temperature | 40 °C      |
| UL                 | Recognized  | CSA                 | Y          |
| Number of Speeds   | 1           |                     |            |

### Technical Specifications

|                       |              |                   |                  |
|-----------------------|--------------|-------------------|------------------|
| Electrical Type       | Three Phase  | Starting Method   | Across The Line  |
| Poles                 | 4            | Rotation          | Counterclockwise |
| Mounting              | Rigid Base   | Drive End Bearing | Ball             |
| Opp Drive End Bearing | Ball         | Frame Material    | Rolled Steel     |
| Shaft Type            | Keyed        | Overall Length    | 26.48 in         |
| Frame Length          | 13.00 in     | Shaft Diameter    | 1.750 in         |
| Shaft Extension       | 8.125 in     |                   |                  |
| Connection Drawing    | 80022801.PCX | Outline Drawing   | E483M2A-S01      |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/12/2021