



Nameplate Specifications

Output HP	30.0 Hp	Output KW	22.4 kW
Frequency	60 Hz	Voltage	200 V
Current	82.2 A	Speed	1770 rpm
Service Factor	1.15	Phase	3
Duty	Continuous	Insulation Class	F
Frame	S286T	Enclosure	Drip Proof
Thermal Protection	None	Ambient Temperature	40 °C
UL	Recognized	CSA	Y
CE	N	Number of Speeds	1

Technical Specifications

Electrical Type	Three Phase	Starting Method	Across The Line
Poles	4	Rotation	Counterclockwise
Mounting	Rigid Base	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Keyed	Overall Length	25.75 in
Frame Length	15.50 in	Shaft Diameter	1.875 in
Shaft Extension	5.09 in		
Connection Drawing	80022803.PCX	Outline Drawing	18771201-001-S01

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/12/2021