



Nameplate Specifications

Output HP	30.0 Hp	Output KW	22.4 kW
Frequency	60 Hz	Voltage	230/460 V
Current	73.2/36.6 A	Speed	1765 rpm
Service Factor	1.15	Phase	3
Duty	Continuous	Insulation Class	F
Frame	Y286T	Enclosure	Drip Proof
Thermal Protection	No Protection	Ambient Temperature	40 °C
UL	Recognized	CSA	Y
CE	N	Number of Speeds	1

Technical Specifications

Electrical Type	Three Phase	Starting Method	Across The Line
Poles	4	Rotation	Counterclockwise
Mounting	Rigid Base	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Keyed	Overall Length	25.75 in
Frame Length	15.50 in	Shaft Diameter	1.875 in
Shaft Extension	5.09 in		
Connection Drawing	80022801.PCX	Outline Drawing	E516M2-S01

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/29/2022