

**Nameplate Specifications**

Phase	3	Output HP	60.0 Hp
Output KW	44.8 kW	Voltage	200 V
Speed	1780 r/min	Service Factor	1.15
Frame	Y364T	Thermal Protection	No Protection
Efficiency	95 %	Ambient Temperature	40 °C
Frequency	60 Hz	Current	165.0 A
Duty	Continuous	Insulation Class	F

Technical Specifications

Rotation	Reversible	Drive End Bearing	314
Opp Drive End Bearing	212		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025