

# PRODUCT INFORMATION PACKET



Model No: E734  
Catalog No: E734  
MODEL-IHP

Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E



**Nameplate Specifications**

|            |            |                     |               |
|------------|------------|---------------------|---------------|
| Phase      | 3          | Output HP           | 60.0 Hp       |
| Output KW  | 44.8 kW    | Voltage             | 200 V         |
| Speed      | 1780 r/min | Service Factor      | 1.15          |
| Frame      | Y364T      | Thermal Protection  | No Protection |
| Efficiency | 95 %       | Ambient Temperature | 40 °C         |
| Frequency  | 60 Hz      | Current             | 165.0 A       |
| Duty       | Continuous | Insulation Class    | F             |

**Technical Specifications**

|                       |            |                   |     |
|-----------------------|------------|-------------------|-----|
| Rotation              | Reversible | Drive End Bearing | 314 |
| Opp Drive End Bearing | 212        |                   |     |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/05/2025