

PRODUCT INFORMATION PACKET

Model No: E924M2

Catalog No: E924M2

General Purpose Motors, Open Drip Proof, 5 HP, 3 Ph, 60 Hz, 575 V, 1755 RPM, 184T



Regal and are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E

Nameplate Specifications

Output HP	5 Hp	Output KW	3.7 kW
Frequency	60 Hz	Voltage	575 V
Current	5.1 A	Speed	1755 rpm
Service Factor	1.15	Phase	3
Duty	Continuous	Insulation Class	F
Frame	184T	Enclosure	Open Drip Proof
Thermal Protection	None	Ambient Temperature	40 °C
UL	Recognized	CSA	Y
CE	Y	Number of Speeds	1

Technical Specifications

Electrical Type	Polyphase	Starting Method	Across The Line
Poles	4	Rotation	Reversible
Mounting	Rigid Base	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Keyed	Overall Length	14.19 in
Frame Length	10.00 in	Shaft Diameter	1.250 in
Shaft Extension	2.85 in		
Outline Drawing	E924M2	Connection Drawing	D0000398-001

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:05/06/2022

