

PRODUCT INFORMATION PACKET



Model No: G151567.60

Catalog No: G151567.60

Obsolete,

replaced by 199975.00 -...15HP..3600RPM.254JM.TEFC.230/460V.3PH.60HZ.CONT.40C..JM PUMP.....

Regal and Leeson are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2023 Regal Rexnord Corporation, All Rights Reserved. MC017097E





Nameplate Specifications

Phase	3	Output HP	15 & 10 Hp
Output KW	11.2 & 7.5 kW	Voltage	208-230/460 & 190/380 V
Speed	3542 & rpm	Service Factor	1.15 & 1.15
Frame	254JM	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Efficiency	91.8 & 90.2 %
Ambient Temperature	40 °C	Frequency	60 & 50 Hz
Current	38.3-35/17.5 & 29/14.5 A	Power Factor	86.9
Duty	Continuous	Insulation Class	F
Design Code	B	KVA Code	G
Drive End Bearing Size	6309	Opp Drive End Bearing Size	6308
UL	Recognized	CSA	Y
CE	Y	IP Code	43
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage Inverter Rated	Starting Method	Wye Start Delta Run Or Inverter
Poles	2	Rotation	Reversible
Mounting	Rigid Base	Motor Orientation	Horizontal
Drive End Bearing	Ball	Opp Drive End Bearing	Ball
Frame Material	Cast Iron	Shaft Type	JM
Assembly/Box Mounting	F1/F2 CAPABLE	Inverter Load	CONSTANT 2:1
Outline Drawing	16991600	Connection Drawing	0080307

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:06/23/2023

