

### Nameplate Specifications

Output HP	2.0 Hp	Output KW	1.5 kW
Frequency	60 Hz	Voltage	208-230/460 V
Current	6.0-5.8/2.9 A	Speed	1725 rpm
Service Factor	1	Phase	3
Duty	Continuous	Insulation Class	B
Frame	X145T	Enclosure	Totally Enclosed Non Ventilated
Thermal Protection	No Protection	Ambient Temperature	65 °C
UL	Recognized	CSA	Y
Number of Speeds	1		

### Technical Specifications

Poles	4	Rotation	Reversible Counterclockwise
Mounting	Rigid Base	Drive End Bearing	Ball
Frame Length	7.50 in	Shaft Diameter	0.875 in
Shaft Extension	SPECIAL in		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:05/24/2022