

Nameplate Specifications

Output HP	3 Hp	Output KW	2.2 kW
Frequency	60 Hz	Voltage	230 V
Current	13 A	Speed	1770 rpm
Service Factor	1.15	Phase	1
Duty	Continuous	Insulation Class	F
Frame	188TC	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	Manual	Ambient Temperature	40 °C
UL	Recognized	CSA	Y
CE	Y	Number of Speeds	1

Technical Specifications

Electrical Type	Capacitor Start Capacitor Run	Starting Method	Across The Line
Poles	4	Rotation	Counterclockwise
Mounting	Rigid Base	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Keyed	Overall Length	15.46 in
Frame Length	10.00 in	Shaft Diameter	1.125 in
Shaft Extension	2.75 in		
Outline Drawing	035910CY	Connection Drawing	005056.03CY

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:09/08/2022