

Nameplate Specifications

Output HP	5.0 Hp	Output KW	3.7 kW
Frequency	60 Hz	Voltage	230/460 V
Current	23.0/11.5 A	Speed	1750 rpm
Service Factor	1	Phase	1
Duty	Continuous	Insulation Class	B
Frame	F213T	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Ambient Temperature	40 °C
UL	Recognized	CSA	Y
CE	N	Number of Speeds	1

Technical Specifications

Electrical Type	Capacitor Start, Capacitor Run, Single Or Dual Voltage	Starting Method	Across The Line
Poles	4	Rotation	Reversible
Mounting	Rigid Base	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Aluminium
Shaft Type	Keyed	Overall Length	17.62 in
Frame Length	7.50 in	Shaft Diameter	1.375 in
Shaft Extension	3.5 in		
Outline Drawing	11448101		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:09/08/2022