

PRODUCT INFORMATION PACKET



Model No: M425M2

Catalog No: M425M2

15 HP, General Purpose Motor, 3 phase, 1800 RPM, 200-230 V, S256T Frame, Drip Proof
General Purpose Motors



Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2021 Regal Rexnord Corporation, All Rights Reserved. MC017097E





Nameplate Specifications

Output HP	15.0/3.7 Hp	Output KW	11.2 kW
Frequency	60 Hz	Voltage	200-230 V
Current	42.5-40.0/16.5-17.0 A	Speed	1760/880 rpm
Service Factor	1.15	Phase	3
Duty	Continuous	Insulation Class	F
Frame	S256T	Enclosure	Drip Proof
Thermal Protection	None	Ambient Temperature	40 °C
UL	Recognized	CSA	Y
CE	N	Number of Speeds	2-1-VT

Technical Specifications

Electrical Type	Three Phase	Starting Method	Across The Line
Poles	4/ 8	Rotation	Counterclockwise
Mounting	Rigid Base	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Keyed	Overall Length	22.10 in
Frame Length	13.00 in	Shaft Diameter	1.625 in
Shaft Extension	4.4 in		
Outline Drawing	80009201-S01	Connection Drawing	80022805.PCX

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/12/2021

