



Nameplate Specifications

Output HP	60 Hp	Output KW	44.8 kW
Frequency	50 Hz	Voltage	380 V
Current	91 A	Speed	1435 rpm
Service Factor	1	Phase	3
Duty	Continuous	Insulation Class	F
Frame	256TY	Enclosure	Open Drip Proof
Thermal Protection	No Protection	Ambient Temperature	60 °C
UL	Recognized	CSA	Y
CE	Y		

Technical Specifications

Poles	4	Rotation	Reversible Clockwise
Drive End Bearing	309	Opp Drive End Bearing	309
Outline Drawing	PL5AA76E40C-S01		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:03/30/2023