

Nameplate Specifications

| | | | |
|------------------------|---------------|----------------------------|-----------------------------|
| Output HP | 40 Hp | Output KW | 30.0 kW |
| Frequency | 50 Hz | Voltage | 400 V |
| Current | 57.1 A | Speed | 989 rpm |
| Service Factor | 1 | Phase | 3 |
| Efficiency | 94.2 % | Power Factor | 0.81 |
| Duty | S1 | Insulation Class | F |
| Frame | 225M | Enclosure | Totally Enclosed Fan Cooled |
| Thermal Protection | No Protection | Ambient Temperature | 40 °C |
| Drive End Bearing Size | 6313 | Opp Drive End Bearing Size | 6213 |
| UL | No | CSA | No |
| CE | Yes | IP Code | 55 |
| Number of Speeds | 1 | Efficiency Class | IE4 |

Technical Specifications

| | | | |
|-----------------------|---------------|-----------------------|----------------|
| Electrical Type | Squirrel Cage | Starting Method | Direct On Line |
| Poles | 6 | Rotation | Bi-Directional |
| Mounting | V1 | Motor Orientation | Shaftdown |
| Drive End Bearing | C3 | Opp Drive End Bearing | C3 |
| Frame Material | Cast Iron | Shaft Type | Keyed |
| Overall Length | 968 mm | Frame Length | 425 mm |
| Shaft Diameter | 60 mm | Shaft Extension | 140 mm |
| Assembly/Box Mounting | Top | | |
| Connection Drawing | 8442000085 | Outline Drawing | 0222500465 |