

### Nameplate Specifications

|                        |                      |                            |                                    |
|------------------------|----------------------|----------------------------|------------------------------------|
| Output HP              | <b>270 Hp</b>        | Output KW                  | <b>200.0 kW</b>                    |
| Frequency              | <b>50 Hz</b>         | Voltage                    | <b>400 V</b>                       |
| Current                | <b>338.2 A</b>       | Speed                      | <b>2984 rpm</b>                    |
| Service Factor         | <b>1</b>             | Phase                      | <b>3</b>                           |
| Efficiency             | <b>96.5 %</b>        | Power Factor               | <b>0.89</b>                        |
| Duty                   | <b>S1</b>            | Insulation Class           | <b>F</b>                           |
| Frame                  | <b>315L</b>          | Enclosure                  | <b>Totally Enclosed Fan Cooled</b> |
| Thermal Protection     | <b>No Protection</b> | Ambient Temperature        | <b>40 °C</b>                       |
| Drive End Bearing Size | <b>6316</b>          | Opp Drive End Bearing Size | <b>6316</b>                        |
| UL                     | <b>No</b>            | CSA                        | <b>No</b>                          |
| CE                     | <b>Yes</b>           | IP Code                    | <b>55</b>                          |
| Number of Speeds       | <b>1</b>             | Efficiency Class           | <b>IE4</b>                         |

### Technical Specifications

|                       |                      |                       |                       |
|-----------------------|----------------------|-----------------------|-----------------------|
| Electrical Type       | <b>Squirrel Cage</b> | Starting Method       | <b>Direct On Line</b> |
| Poles                 | <b>2</b>             | Rotation              | <b>Bi-Directional</b> |
| Mounting              | <b>B3</b>            | Motor Orientation     | <b>Horizontal</b>     |
| Drive End Bearing     | <b>C3</b>            | Opp Drive End Bearing | <b>C3</b>             |
| Frame Material        | <b>Cast Iron</b>     | Shaft Type            | <b>Keyed</b>          |
| Overall Length        | <b>1287 mm</b>       | Frame Length          | <b>840 mm</b>         |
| Shaft Diameter        | <b>65 mm</b>         | Shaft Extension       | <b>140 mm</b>         |
| Assembly/Box Mounting | <b>Top</b>           |                       |                       |
| Connection Drawing    | <b>8442000085</b>    | Outline Drawing       | <b>0231500881</b>     |