



**Nameplate Specifications**

Phase	3	Output HP	5.0 Hp
Output KW	3.7 kW	Voltage	190/380//220/440 V
Speed	2850//3500 rpm	Service Factor	1
Frame	182TDZTDZ	Enclosure	Drip Proof
Thermal Protection	No Protection	Efficiency	86.5 %
Ambient Temperature	40 °C	Frequency	50 Hz
Current	14.4/7.6//13/6.5 A	Duty	Continuous
Insulation Class	F	UL	Recognized
CSA	Y	CE	Y
Number of Speeds	1		

**Technical Specifications**

Poles	2	Rotation	Reversible
Mounting	Special/Non-Standard	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Keyed	Frame Length	9.00 in
Shaft Diameter	1.000 in	Shaft Extension	3 in
Outline Drawing	SS600253		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:08/16/2023