

Nameplate Specifications

| | | | |
|------------------------|---------------|----------------------------|-----------------------------|
| Output HP | 20 Hp | Output KW | 15.0 kW |
| Frequency | 50 Hz | Voltage | 415 V |
| Current | 32.2 A | Speed | 730 rpm |
| Service Factor | 1 | Phase | 3 |
| Efficiency | 88 % | Power Factor | 0.736 |
| Duty | S1 | Insulation Class | F |
| Frame | 200L | Enclosure | Totally Enclosed Fan Cooled |
| Thermal Protection | No Protection | Ambient Temperature | 50 °C |
| Drive End Bearing Size | 6312 | Opp Drive End Bearing Size | 6212 |
| UL | No | CSA | No |
| CE | Yes | IP Code | 55 |
| Number of Speeds | 1 | Efficiency Class | IE2 |

Technical Specifications

| | | | |
|-----------------------|---------------|-----------------------|----------------|
| Electrical Type | Squirrel Cage | Starting Method | Direct On Line |
| Poles | 8 | Rotation | Bi-Directional |
| Mounting | B5 | Motor Orientation | Horizontal |
| Drive End Bearing | C3 | Opp Drive End Bearing | C3 |
| Frame Material | Cast Iron | Shaft Type | Keyed |
| Overall Length | 769 mm | Frame Length | 370 mm |
| Shaft Diameter | 55 mm | Shaft Extension | 110 mm |
| Assembly/Box Mounting | TOP | | |
| Connection Drawing | 8442000085 | Outline Drawing | 0220000599 |