

## Nameplate Specifications

|                        |               |                            |                             |
|------------------------|---------------|----------------------------|-----------------------------|
| Output HP              | 335 Hp        | Output KW                  | 250.0 kW                    |
| Frequency              | 50 Hz         | Voltage                    | 380/660 V                   |
| Current                | 444.3 A       | Speed                      | 2983 rpm                    |
| Service Factor         | 1             | Phase                      | 3                           |
| Efficiency             | 95 %          | Power Factor               | 0.90                        |
| Duty                   | S1            | Insulation Class           | F                           |
| Frame                  | 355M          | Enclosure                  | Totally Enclosed Fan Cooled |
| Thermal Protection     | No Protection | Ambient Temperature        | 40 °C                       |
| Drive End Bearing Size | 6317          | Opp Drive End Bearing Size | 6317                        |
| UL                     | No            | CSA                        | No                          |
| CE                     | Yes           | IP Code                    | 55                          |
| Number of Speeds       | 1             | Efficiency Class           | IE2                         |

## Technical Specifications

|                       |               |                       |                |
|-----------------------|---------------|-----------------------|----------------|
| Electrical Type       | Squirrel Cage | Starting Method       | Direct On Line |
| Poles                 | 2             | Rotation              | Bi-Directional |
| Mounting              | B5            | Motor Orientation     | Horizontal     |
| Drive End Bearing     | C3            | Opp Drive End Bearing | C3             |
| Frame Material        | Cast Iron     | Shaft Type            | Keyed          |
| Overall Length        | 1512 mm       | Frame Length          | 1010 mm        |
| Shaft Diameter        | 75 mm         | Shaft Extension       | 140 mm         |
| Assembly/Box Mounting | Top           |                       |                |
| Connection Drawing    | 8442000085    | Outline Drawing       | 0235501826     |