

PRODUCT INFORMATION PACKET

Model No: T350
Catalog No: T350
MODEL-IHP

Regal and are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E



Nameplate Specifications

Output HP	5.5KW Hp	Frequency	60 Hz
Voltage	230/460 V	Current	20.0/10.0 A
Speed	1755 rpm	Phase	3
Duty	Continuous	Insulation Class	F
Frame	P132S	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Ambient Temperature	40 °C
UL	Recognized	Number of Speeds	1

Technical Specifications

Rotation	Reversible	Mounting	Round
Drive End Bearing	Ball	Opp Drive End Bearing	Ball

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:05/24/2022