

### Nameplate Specifications

|                        |               |                            |                             |
|------------------------|---------------|----------------------------|-----------------------------|
| Phase                  | 3             | Output HP                  | 5.50 Hp                     |
| Output KW              | 4.0 kW        | Voltage                    | 415 V                       |
| Speed                  | 2908 rpm      | Service Factor             | 1                           |
| Frame                  | 112M          | Enclosure                  | Totally Enclosed Fan Cooled |
| Thermal Protection     | No Protection | Efficiency                 | 88.1 %                      |
| Ambient Temperature    | 50 °C         | Frequency                  | 50 Hz                       |
| Current                | 6.8 A         | Power Factor               | 0.93                        |
| Duty                   | S1            | Insulation Class           | F                           |
| Drive End Bearing Size | 6306          | Opp Drive End Bearing Size | 6206                        |
| UL                     | No            | CSA                        | No                          |
| CE                     | Yes           | IP Code                    | 55                          |
| Number of Speeds       | 1             | Efficiency Class           | IE3                         |

### Technical Specifications

|                       |               |                       |                |
|-----------------------|---------------|-----------------------|----------------|
| Electrical Type       | Squirrel Cage | Starting Method       | Direct On Line |
| Poles                 | 2             | Rotation              | Bi-Directional |
| Mounting              | B35           | Motor Orientation     | Horizontal     |
| Drive End Bearing     | 2z-C3         | Opp Drive End Bearing | 2z-C3          |
| Frame Material        | Cast Iron     | Shaft Type            | Keyed          |
| Overall Length        | 399 mm        | Frame Length          | 174 mm         |
| Shaft Diameter        | 28 mm         | Shaft Extension       | 60 mm          |
| Assembly/Box Mounting | Top           |                       |                |
| Connection Drawing    | 8442000085    |                       |                |