



### Nameplate Specifications

|                        |               |                            |                             |
|------------------------|---------------|----------------------------|-----------------------------|
| Phase                  | 3             | Output HP                  | 60 Hp                       |
| Output KW              | 45.0 kW       | Voltage                    | 400 V                       |
| Speed                  | 742 r/min     | Service Factor             | 1                           |
| Frame                  | 280M          | Enclosure                  | Totally Enclosed Fan Cooled |
| Thermal Protection     | No Protection | Efficiency                 | 92.2 %                      |
| Ambient Temperature    | 40 °C         | Frequency                  | 50 Hz                       |
| Current                | 91.5 A        | Power Factor               | 0.77                        |
| Duty                   | S1            | Insulation Class           | F                           |
| Drive End Bearing Size | 6317          | Opp Drive End Bearing Size | 6317                        |
| UL                     | No            | CSA                        | No                          |
| CE                     | Yes           | IP Code                    | 55                          |
| Efficiency Class       | IE3           |                            |                             |

### Technical Specifications

|                       |               |                       |                |
|-----------------------|---------------|-----------------------|----------------|
| Electrical Type       | Squirrel Cage | Starting Method       | Direct On Line |
| Poles                 | 8             | Rotation              | Bi-Directional |
| Mounting              | B35           | Motor Orientation     | Horizontal     |
| Drive End Bearing     | C3            | Opp Drive End Bearing | C3             |
| Frame Material        | Cast Iron     | Shaft Type            | Keyed          |
| Overall Length        | 1111 mm       | Frame Length          | 600 mm         |
| Shaft Diameter        | 75 mm         | Shaft Extension       | 140 mm         |
| Assembly/Box Mounting | Top           |                       |                |
| Outline Drawing       | 0228000590    | Connection Drawing    | 8442000085     |