

### Nameplate Specifications

|                        |               |                            |                             |
|------------------------|---------------|----------------------------|-----------------------------|
| Output HP              | 10 Hp         | Output KW                  | 7.5 kW                      |
| Frequency              | 50 Hz         | Voltage                    | 380 V                       |
| Current                | 15.2 A        | Speed                      | 1470 rpm                    |
| Service Factor         | 1             | Phase                      | 3                           |
| Efficiency             | 90.4 %        | Power Factor               | 0.83                        |
| Duty                   | S1            | Insulation Class           | F                           |
| Frame                  | 132M          | Enclosure                  | Totally Enclosed Fan Cooled |
| Thermal Protection     | No Protection | Ambient Temperature        | 40 °C                       |
| Drive End Bearing Size | 6308          | Opp Drive End Bearing Size | 6208                        |
| UL                     | No            | CSA                        | No                          |
| CE                     | Yes           | IP Code                    | 55                          |
| Number of Speeds       | 1             | Efficiency Class           | IE3                         |

### Technical Specifications

|                       |               |                       |                |
|-----------------------|---------------|-----------------------|----------------|
| Electrical Type       | Squirrel Cage | Starting Method       | Direct On Line |
| Poles                 | 4             | Rotation              | Bi-Directional |
| Mounting              | V1            | Motor Orientation     | Shaftdown      |
| Drive End Bearing     | 2Z-C3         | Opp Drive End Bearing | 2Z-C3          |
| Frame Material        | Cast Iron     | Shaft Type            | Keyed          |
| Overall Length        | 567 mm        | Frame Length          | 240 mm         |
| Shaft Diameter        | 38 mm         | Shaft Extension       | 80 mm          |
| Assembly/Box Mounting | Top           |                       |                |
| Connection Drawing    | 8442000085    | Outline Drawing       | 0213200595     |