

Nameplate Specifications

| | | | |
|------------------------|---------------|----------------------------|-----------------------------|
| Output HP | 60 Hp | Output KW | 45.0 kW |
| Frequency | 50 Hz | Voltage | 400 V |
| Current | 79.4 A | Speed | 2976 rpm |
| Service Factor | 1 | Phase | 3 |
| Efficiency | 94 % | Power Factor | 0.87 |
| Duty | S1 | Insulation Class | F |
| Frame | 225M | Enclosure | Totally Enclosed Fan Cooled |
| Thermal Protection | No Protection | Ambient Temperature | 40 °C |
| Drive End Bearing Size | 6313 | Opp Drive End Bearing Size | 6213 |
| UL | No | CSA | No |
| CE | Yes | IP Code | IP55 |
| Number of Speeds | 3 | | |

Technical Specifications

| | | | |
|-----------------------|---------------|-----------------------|----------------|
| Electrical Type | Squirrel Cage | Starting Method | Direct On Line |
| Poles | 2 | Rotation | Bi-Directional |
| Mounting | B3 | Motor Orientation | Horizontal |
| Drive End Bearing | 2z-C3 | Opp Drive End Bearing | 2z-C3 |
| Frame Material | Cast Iron | Shaft Type | Keyed |
| Overall Length | 832 mm | Frame Length | 425 mm |
| Shaft Diameter | 55.000 mm | Shaft Extension | 110 mm |
| Assembly/Box Mounting | Top | | |
| Connection Drawing | 8442000085 | Outline Drawing | 0222500457 |