

**Nameplate Specifications**

Phase	3	Output HP	40 Hp
Voltage	230 / 460 V	Speed	3530 rpm
Service Factor	1.15	Frame	324TSC
Enclosure	Totally Enclosed Fan Cooled	Thermal Protection	No Protection
Efficiency	92.4 %	Ambient Temperature	40 °C
Frequency	60 Hz	Current	93.4 / 46.7 A
Duty	Continuous	Insulation Class	F
Number of Speeds	1		

**Technical Specifications**

Poles	2	Rotation	Reversible
Mounting	Round	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Cast Iron
Shaft Type	Keyed	Shaft Diameter	1.875 in
Shaft Extension	3.5 in		
Outline Drawing	TCF82012E-S01		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/26/2023