



Nameplate Specifications

Phase	3	Output HP	50 Hp
Voltage	230 / 460 V	Speed	1770 rpm
Service Factor	1.15	Frame	326TC
Enclosure	Totally Enclosed Fan Cooled	Thermal Protection	No Protection
Efficiency	94.5 %	Ambient Temperature	40 °C
Frequency	60 Hz	Current	118.0 / 59.0 A
Duty	Continuous	Insulation Class	F
Number of Speeds	1		

Technical Specifications

Poles	4	Rotation	Reversible
Mounting	Round	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Cast Iron
Shaft Type	Keyed	Shaft Diameter	2.125 in
Shaft Extension	5 in		
Outline Drawing	TCF82038E-S01		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/26/2023