



Nameplate Specifications

Phase	3	Output HP	60 Hp
Voltage	230 / 460 V	Speed	1770 rpm
Service Factor	1.15	Frame	364TC
Enclosure	Totally Enclosed Fan Cooled	Thermal Protection	No Protection
Efficiency	95 %	Ambient Temperature	40 °C
Frequency	60 Hz	Current	143.0 / 71.5 A
Duty	Continuous	Insulation Class	F
Number of Speeds	1		

Technical Specifications

Poles	4	Rotation	Reversible
Mounting	Round	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Cast Iron
Shaft Type	Keyed	Shaft Diameter	2.375 in
Shaft Extension	5.62 in		
Outline Drawing	TCF82039E-S01		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/26/2023