



Nameplate Specifications

| | | | |
|------------------|------------------------------------|---------------------|-----------------------|
| Phase | 3 | Output HP | 60 Hp |
| Voltage | 230 / 460 V | Speed | 1180 rpm |
| Service Factor | 1.15 | Frame | 404TC |
| Enclosure | Totally Enclosed Fan Cooled | Thermal Protection | No Protection |
| Efficiency | 94.5 % | Ambient Temperature | 40 °C |
| Frequency | 60 Hz | Current | 148.0 / 74.0 A |
| Duty | Continuous | Insulation Class | F |
| Number of Speeds | 1 | | |

Technical Specifications

| | | | |
|-------------------|----------------------|-----------------------|--------------|
| Poles | 6 | Mounting | F1 |
| Drive End Bearing | Ball | Opp Drive End Bearing | Ball |
| Frame Material | Cast Iron | Shaft Type | Keyed |
| Shaft Diameter | 2.875 in | Shaft Extension | 7 in |
| Outline Drawing | TCF82064E-S01 | | |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/26/2023