

### Nameplate Specifications

|                        |               |                            |                             |
|------------------------|---------------|----------------------------|-----------------------------|
| Output HP              | 15 Hp         | Output KW                  | 11.0 kW                     |
| Frequency              | 50 Hz         | Voltage                    | 400/690 V                   |
| Current                | 24.5 A        | Speed                      | 730 rpm                     |
| Service Factor         | 1             | Phase                      | 3                           |
| Efficiency             | 88.6 %        | Power Factor               | 0.73                        |
| Duty                   | S1            | Insulation Class           | H                           |
| Frame                  | 180L          | Enclosure                  | Totally Enclosed Fan Cooled |
| Thermal Protection     | No Protection | Ambient Temperature        | 40 °C                       |
| Drive End Bearing Size | 6311          | Opp Drive End Bearing Size | 6211                        |
| UL                     | NO            | CSA                        | NO                          |
| CE                     | YES           | IP Code                    | 66                          |
| Number of Speeds       | 1             | Efficiency Class           | IE3                         |

### Technical Specifications

|                       |               |                       |                |
|-----------------------|---------------|-----------------------|----------------|
| Electrical Type       | Squirrel Cage | Starting Method       | Direct On Line |
| Poles                 | 8             | Rotation              | Bi-Directional |
| Mounting              | B3            | Motor Orientation     | Horizontal     |
| Drive End Bearing     | C3            | Opp Drive End Bearing | C3             |
| Frame Material        | Cast Iron     | Shaft Type            | Keyed          |
| Overall Length        | 750 mm        | Frame Length          | 366 mm         |
| Shaft Diameter        | 48 mm         | Shaft Extension       | 110 mm         |
| Assembly/Box Mounting | RHS           |                       |                |
| Outline Drawing       | 0218000824    | Connection Drawing    | 8442000085     |