

Nameplate Specifications

| | | | |
|------------------------|----------------------|----------------------------|------------------------------------|
| Output HP | 30 Hp | Output KW | 22.0 kW |
| Frequency | 50 Hz | Voltage | 400/690 V |
| Current | 39.4 A | Speed | 2961 rpm |
| Service Factor | 1 | Phase | 3 |
| Efficiency | 92.7 % | Power Factor | 0.87 |
| Duty | S1 | Insulation Class | H |
| Frame | 180M | Enclosure | Totally Enclosed Fan Cooled |
| Thermal Protection | No Protection | Ambient Temperature | 40 °C |
| Drive End Bearing Size | 6311 | Opp Drive End Bearing Size | 6211 |
| UL | NO | CSA | NO |
| CE | YES | IP Code | 66 |
| Number of Speeds | 1 | Efficiency Class | IE3 |

Technical Specifications

| | | | |
|-----------------------|----------------------|-----------------------|-----------------------|
| Electrical Type | Squirrel Cage | Starting Method | Direct On Line |
| Poles | 2 | Rotation | Bi-Directional |
| Mounting | B5 | Motor Orientation | Horizontal |
| Drive End Bearing | C3 | Opp Drive End Bearing | C3 |
| Frame Material | Cast Iron | Shaft Type | Keyed |
| Overall Length | 712 mm | Frame Length | 328 mm |
| Shaft Diameter | 48 mm | Shaft Extension | 110 mm |
| Assembly/Box Mounting | TOP | | |
| Outline Drawing | 0218000821 | Connection Drawing | 8442000085 |